

# Scintillation Probe 2002

- high sensitivity
- large detector surface
- application fields:
  - nuclear medicine
  - environmental monitoring
  - security controls  
(police, customs, border authorities, factory inspectorates)
- by means of a probe cable connectible to
  - the dose rate meter „X 5 C plus“ (as well as to the predecessor models „X 5 C“, „X 5 DE“ and „X 50 DE“), identified as pulse probe
  - the contamination monitor “CoMo 170”
- power supply from the basic unit

## Technical Data

Type of radiation:	$\beta$ , $\gamma$
Energy range:	$\gamma$ -radiation and X-rays: 25 keV – 2 MeV $\beta$ -radiation: >100 keV
Detector:	(70 x 70 x 13) mm NaJ (Tl)-scintillator with photo multiplier
Reference orientation:	vertical onto the square surface
Position of the detector:	middle of the detector cap
Reference point:	middle of the square surface
Background count rate*:	approx. 100 cps
Range of relative humidity:	0 up to 90%, no influence
Range of outside air pressure:	600 up to 1300 hPa, influence negligible
Indication ranges:	0 – 200 cps 200 – 2000 cps 2 – 20 kcps (20 kcps $\cong$ 13 $\mu$ Sv/h referred to Cs 137)
Temperature range:	operation: -20 °C up to +50 °C storage: -30 °C up to +60 °C (NOTE: max. temperature change 10 °C/h)
Overload capacity:	up to approx. 3 mSv/h (referred to Cs 137)
After effect:	after exposure to radiation of 3 mSv/h, error after 20 minutes is approx. 5%
Voltage supply:	+5V from the basic unit
Housing:	aluminium, partly anodically oxidized, protection class IP 65 (hose-proof)
Dimensions:	(80 x 85 x 35) mm with 200 mm handle ( $\varnothing$ 33 mm)
Weight:	530 g

\* at 0,1  $\mu$ Sv/h



Distributore ufficiale per l'Italia

**Extratech** Engineering, Technology, Software & Training - by **3DLiFe srl**  
Via Torraca, 76 - 85100 Potenza (PZ) Tel/Fax. (+39) 0971.21.432 p.iva 016.540.40.763  
www.extratech.it - info@extratech.it - www.3dlife.it - info@3dlife.it

rif: Ing. Vito Lisanti cell. 329.80.380.79